

[See all 10 Products in Family](#)

UV-VIS-NIR Nd:YAG Dual Camera Laser Line Vertical Mitutoyo Video Microscope Unit

See More by [Mitutoyo](#)



Stock **#71-019** **1 In Stock**

-

1

+

C\$19,460⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$19,460.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
378-514	Model Number:
UV-VIS-NIR	Range:
Vertical Mount, Brightfield, Erect Image	Type:
Mitutoyo	Manufacturer:

Compatible Objectives: MPlan Apo/HR/SL, MPlan NIR/NUV, and MPlan UV	
Note: Note: Magnification: 1X Tube Lens Optional C-Mount adapter #37-044 available for dual-camera system	
Physical & Mechanical Properties	
1300.00	Weight (g):
Optical Properties	
226, 355, 532, 1064	Design Wavelength DWL (nm):
1X	Magnification:
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
C-Mount	Mount:
Objective Mounts: M26 x 36 TPI	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Designed for use with [Mitutoyo NIR, NUV, and UV Infinity Corrected Objectives](#)
- Maximum Sensor Size up to 2/3"
- Ideal for Laser Processing and Machining applications

Mitutoyo Nd:YAG Laser Line Video Microscope Units (VMU) allow for quick and easy setup of laser processing systems by connecting an infinity corrected objective to a c-mount camera. Optimized for Nd:YAG laser lines of 266, 355, 532, and 1064nm, these VMUs are designed for use with [Mitutoyo UV, NUV, and NIR infinity corrected objectives](#). These VMUs can also be used as infrared inspection systems when using an infrared light source and an infrared camera. Mitutoyo Nd:YAG Laser Line Video Microscope Units (VMU) are ideal for laser processing and imaging applications such as cutting, trimming, and repair of IC wiring, thin-film processing, and infrared spectral characteristic analysis. A dual-camera laser line VMU option is also available for high and low magnification observation.