


## WinCamD-IR-BB, 30 Hz Broadband Beam Profiler



#24-211 WnCamD-LCMBeam Profiler

Stock **#29-184** **2 In Stock**

⊖ 1 ⊕ C\$30,800<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$30,800.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

S-WCD-IR-BB-30 **Model Number:**

### Physical & Mechanical Properties

73 x 73 x 52 **Dimensions (mm):**

±5µm **Dimensional Accuracy:**

### Optical Properties

2000 - 16000 **Spectral Range:**

170 (min) **Beam Diameter (µm):**

## Sensor

17 x 17 **Pixel Size, H x V (µm):**

640 x 480 **Pixels (H x V):**

10.88 x 8.16 **Sensing Area, H x V (mm):**

30 **Frame Rate:**

## Electrical

≥1000:1 **Signal to Noise S/N Ratio (dB):**

30 dB optical / 60 dB electrical **Peak Noise (nW/cm<sup>2</sup>):**

## Threading & Mounting

1/4"-20 holes aligned with sensor center **Mount:**

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **REACH 241:**

## Product Details

- Designed for Use from 355 to 16000nm
- Compatible with Beam Diameters Down to 52µm
- Robust and Easy to Use Free Software [Provided](#)
- Measure Beam Wander, M<sup>2</sup>, Divergence, and More

DataRay Camera Beam Profilers provide excellent solutions for beam analysis of both continuous wave and pulsed laser sources. Each beam profiler features an integrated CMOS sensor (IR profilers feature Microbolometer sensors) that eliminates comet trailing for higher resolution output and allows for update rates of 60+ Hz. Sensors are available with active sizes of 6.6, 11.3, and 25mm horizontals, enabling measurement of large beam diameters. DataRay Camera Beam Profilers have the added advantage of a free, robust software with analysis features such as M<sup>2</sup> measurement, beam wander and logging, and instrument alignment. These profilers are USB3.0/2.0 powered and include a 3m flexible screw locking cable. Neutral density filters with optical densities of 1.0, 2.0, and 4.0 are included.