


[See all 6 Products in Family](#)

ZAP-IT[®] Laser Alignment Paper, 2 x 5", Box of 50 Sheets



Stock **#15-826** **13 In Stock**

-

1

+

C\$183^{.40}

ADD TO CART

Volume Pricing	
Qty 1-5	C\$183.40 each
Qty 6-24	C\$165.20 each
Need More?	Request Quote

Product Downloads

General

Model Number:

ZAP-25-50

Note:

Recommended Pulsed Width: 1ns to 30ms
Recommended Power Level Range: 5 mJ/cm² to 20 J/cm²

Physical & Mechanical Properties

Thickness (inches):

0.009

0.24	Thickness (mm):
2 x5	Sheet Size (in):
50.8 x127	Sheet Size (mm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Industrial Standard Beam Profile Viewing Paper
 - Records Beam Shape, Divergence, Mode, and Intensity Profile of Pulsed Lasers
 - Suitable for Broadband Sources from UV to IR
- ZAP-IT® Laser Alignment Paper is designed to test the characteristics of pulsed laser sources from the ultraviolet to infrared. Beam characteristics are recorded by holding the ZAP-IT® Laser Alignment Paper in the beam path. ZAP-IT® Laser Alignment Paper is ideal for use in alignment applications or with [laser optics](#) including laser beam expanders, optical lenses, apertures, attenuators, or power meters. For continuous wave lasers, use a mechanical chopper, Q-switch, or manually switch the laser on and off rapidly to create short pulses.
- Note:** It may be difficult to see the beam characteristics when the input beam diameter is 1/4"/6.35mm or less. If so, use a [beam expander](#) or [plano convex lens](#) to magnify the beam diameter. If using a plano convex lens, place ZAP-IT® Laser Alignment Paper at an image distance of 2.5 times longer than the focal length of the lens.