

[See all 43 Products in Family](#)

Power Supply for 0.5-0.8mW HeNe Laser, AC, Bare Wire Leads



AC with Bare Leads HeNe Power Supply (#11-379, #11-380)

Stock **#11-379** [CONTACT US](#)

-

1

+

C\$663⁶⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$663.60 each
Need More?	Request Quote

Product Downloads



General

OEM

Type:

[1108](#), [1108P](#), [1107](#), [1107P](#)

Compatible Laser Models:

L92 Series

Model Number:

[#62-714](#), [#62-715](#), [#62-716](#), [#62-717](#)

Compatible Laser Stock Number:

CDRH Delay (3-5 seconds)

Features:

Physical & Mechanical Properties	
4.25 x 3.30 x 1.20	Dimensions (inches):
Electrical	
5	Output Power (W):
0.55/0.32	Input Current (A):
Hardware & Interface Connectivity	
1250	Output Voltage (V):
4	Output Current (mA):
High Voltage Alden Connector	Connector:
100/110/220 (AC)	Input Voltage (V):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

