

SCHOTT N-WG295, 50mm Sq., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-465** ☐ In Stock



1



C\$108.50

ADD TO CART

Qty 1-10

C\$108.50

Qty 11+

C\$106.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Cut-On Wavelength (nm):
295.00 ±6

Density (g/cm³):

2.51
Glass/Filter Number: SCHOTT N-WG295
Length (mm): 50.00
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 400
Index of Refraction n_d: 1.52
Spectral Transmittance t_p (%): 99
Stopband Limit λ_s(nm): 250
Surface Quality: 60-40
Transformation Temperature (°C): 565
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: UV
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View