


[See all 66 Products in Family](#)

[All Products](#) / [Optics](#) / [SCHOTT Optical Components](#)
/ [SCHOTT NG Absorptive Neutral Density \(ND\) Filters](#)

SCHOTT NG11, 0.1 OD, 12.5mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock #16-717 **20+ In Stock**

1 C\$37^{.80}

ADD TO CART

Volume Pricing	
Qty 1-10	C\$37.80 each
Qty 11-49	C\$33.60 each
Need More?	Request Quote

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
eDrawing:eprt	
EO Spec Sheet	Download All

General

Type: Neutral Density Filter

Physical & Mechanical Properties

Diameter (mm): 12.50

Thickness (mm): 0.60 (nominal)

Dimensional Tolerance (mm): ±0.38

Optical Properties

Optical Density OD (Average): 0.1 ±0.006 @ 546nm

Glass/Filter Number: **SCHOTT NG11**

Coating: Uncoated

Index of Refraction (n_d): 1.50

Surface Quality: 80-50

Transmission (%): 79.43 ±1.03% @ 546nm

Wavelength Range (nm): 400 - 700

Material Properties

Transformation Temperature (°C): 481

Regulatory Compliance

Certificate of Conformance: [View](#)

Reach 240: **Compliant**

Product Details

- Tightly Controlled Transmission Specifications
- NG4, NG9, or NG11 Glass Types
- Specified Optical Densities from 0.15 to 5.0
- Provide Even Light Attenuation in the Visible Spectrum
- **SCHOTT NG Gray Glass** Also Available

SCHOTT NG Absorptive Neutral Density (ND) Filters consist of NG4, NG9, or NG11 SCHOTT glass types and provide even light attenuation through absorption in the visible spectrum. These filters are manufactured to achieve a specified optical density, ranging from 0.15 to 5.0, to simplify integration into optical systems. SCHOTT NG Absorptive Neutral Density (ND) Filters are available in a standard 50 x 50mm size and multiple filters can be stacked to achieve custom optical densities. Custom sizes from 5 to 160mm as well as custom optical densities or transmission values for specific wavelengths are available on request; for more information, visit our [Colored Glass Filter Manufacturing](#) capabilities webpage. [SCHOTT NG Gray Glass Filters](#) are also available.

Each filter lot is measured and thickness is adjusted to meet the specified transmission value at 546nm. Variations in filter lot performance can result in variations in nominal thickness; however, the transmission variations between lots will be minimal.

Filter Simulation Software

[Click here](#) to download SCHOTT's colored glass filter calculation program which can be used to calculate the internal transmittance and external transmission of each SCHOTT glass type. The program can simulate the performance of individual filters with user specified thickness or of stacked filters with varying glass types and thicknesses.

Technical Information

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	12.5mm Dia., SCHOTT NG Absorptive ND Filter Kit (14 Filters)		#15-094	C\$387.80 Request Quote	CONTACT US 1
MORE+	25mm Dia., SCHOTT NG Absorptive ND Filter Kit (14 Filters)		#15-095	C\$714.00 Request Quote	CONTACT US 1
MORE+	50mm Sq., SCHOTT NG Absorptive ND Filter Kit (14 Filters)		#15-096	C\$1,533.00 Request Quote	1 In Stock 1

Quote Your Size

PLEASE ENTER YOUR REQUIRED SPECIFICATIONS HERE:

Glass Type

BG

Filter Number

Thickness (mm)

Shape

Diameter (mm)

0

Length (mm)

0

Width (mm)

0

Quantity

0

[GET PRICING](#)

General Information SCHOTT Optical Filter Glass:

BG	Blue, blue-green, and multiband glasses
GG	Nearly colorless to yellow glasses, IR transmitting
KG	Virtually colorless glasses with high transmission in the visible and absorption in the IR
NG	Neutral density glasses with uniform attenuation in the visible range
OG	Orange glasses, IR transmitting
RG	Red and black glasses, blocking visible, IR transmitting
UG	Black and blue glasses, UV transmitting
VG	Green glasses
WG	Colorless glasses with different cut-offs in the UV, transmitting in the visible and IR ranges

Note: The spectral curves above show the internal transmittance of the individual optical filter glasses

[ADDITIONAL CAPABILITIES](#)

Standard Manufacturing Tolerances:

Edge length and diameter	+/-0.2 mm
Thickness	For ≤ 1mm: ± 0.1mm For > 1 – 3mm: ± 0.2mm
Surface Quality	60 – 40
Surface Accuracy	≤8 Waves
Parallelism	≤3 arcmin
Clear Aperture	≥90%
Edges & Bevels	Round parts ≥ Ø5mm: polished edges & protective bevel Square & rectangular parts < 50 x 50mm: polished edges, no bevel
Edge Chips	For ≤ Ø80mm: < 0.3mm (5/E0.3), for ≥ Ø81mm < 0.6mm (5/E0.6)

Surface quality according to DIN ISO 10110:

Polishing quality	P2
Defects	5/3 x 0.63
All edges machined	
Round filters with chamfer max. 0.5mm, square and rectangular < 50x50mm without chamfer	
Edge chips permitted up to 5/E0.3	

Frequently Purchased Together




#43-794 - 1.0" x 1.0", FL 0.37", IR Fresnel Lens
C\$55.30

Qty



#45-599 - 10mm Dia. UV Enhanced Aluminum, λ/4 Mirror
C\$89.60

Qty



#48-389 - 12.5mm Dia 30R/70T, NIR Plate Beamsplitter
C\$187.60





















Qty



#62-979 - 650nm 12.5mm Dia., High Performance Longpass Filter
C\$278.60

Qty

Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	5.0 - 25.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed		#55-529	C\$142.80 Request Quote	20+ In Stock <input type="text" value="1"/> 
MORE+ 	7.0 - 40.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-676	C\$148.40 Request Quote	20+ In Stock <input type="text" value="1"/> 
MORE+ 	10.0 - 60.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed		#55-530	C\$151.20 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	7.0 - 67.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-669	C\$162.40 Request Quote	20+ In Stock <input type="text" value="1"/> 
MORE+ 	8.0 - 118.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-666	C\$168.00 Request Quote	20+ In Stock <input type="text" value="1"/> 
MORE+ 	4.0 - 36.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-077	C\$219.80 Request Quote	5 In Stock <input type="text" value="1"/> 
MORE+ 	12.5/12.7mm Optic Dia., X-Y Translating Optic Mount	Adjustable - Linear (XY)		#62-955	C\$365.40 Request Quote	5 In Stock <input type="text" value="1"/> 
MORE+ 	5.0 - 100.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-078	C\$574.00 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	12.5/12.7mm Optic Dia., Precision Gimbal Mount	Adjustable - Gimbal		#84-640	C\$589.40 Request Quote	7 In Stock <input type="text" value="1"/> 
MORE+ 	12.5/12.7mm Optic Dia., X-Y-Z Translating Optic Mount	Adjustable - Linear (XYZ)		#62-958	C\$600.60 Request Quote	5 In Stock <input type="text" value="1"/> 

Check out our full selection of mounts [here](#).

Resources

Media Type

- Application Note
- FAQ
- Glossary
- Video

APPLICATION NOTE

Understanding Neutral Density Filters

? FAQ

What is an ND Filter?

? FAQ

Can I place ND filters back-to-back and increase...

? FAQ

? FAQ

GLOSSARY

What is the difference between using an absorptiv...

How should I orient my reflective ND or interferenc...

Continuously Variable Apodizing Filter

[View More](#)
