

Optical Chopper (115 VAC)



Standard Optical Chopper, #55-783

Stock **#55-783** ☐ In Stock

-

1

+

C\$2,317.00

ADD TO CART

Qty 1+

C\$2,317.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Connector:

5 VHCT TTL Pulse via BNC

Dimensions (mm):

Control Unit: 254 W x 76 H x 178 D

Weight (kg):

Control Unit: 2.6

Temperature Coefficient @ 25°C (%/°C):

±0.01

Frequency Stability (%):

Short Term: See blade specification for phase jitter

Long Term: ±0.1% of maximum frequency
Mark-Space Ratio: 1:1 When Using 1 Blade
Slot Variants Included: 2, 5, 10, 30, 200
Note: Compatible Discs: #56-066 , #56-067 , #56-068 , #56-069 , #56-070 , #56-071
Operating Voltage (V): 115

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View