

Swivel Arm



#03-684 Swivel Arm

Stock **#03-684** 5 In Stock

-

1

+

C\$147⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$147.00 each
Need More?	Request Quote

Product Downloads

General

Mounting Adapter

Type:

Physical & Mechanical Properties

127 x 38.1 x 38.1

Dimensions (mm):

Black Anodized Aluminum with Stainless Steel Post

Construction:

1.19

Weight (lbs):

1.5 Wx5 L x1.5 H		Dimensions (inches):
Regulatory Compliance		
Compliant	RoHS 2015:	
	Certificate of Conformance:	
View		

Product Details


- Swivel Arm for Added Flexibility
- 90° Angle Mounts Connect Horizontal Arms onto Vertical Posts
- Ring Mounts for Increased Versatility
- [Imaging System Bases](#), [Rack and Pinion Focusing Mounts](#), and [Stainless Steel Posts](#) Also Available

Accessories for Imaging Systems are available to increase the versatility of an imaging system. Products in this family include a swivel arm, Infinity Microscope, 90° angle mount, and ring mounts. The swivel arm adds an axis of rotation to the rack and pinion-focusing mounts. The swivel arm can rotate around a vertical post, and the rack and pinion focus mount can rotate around the 3/4" post attached to the swivel arm. The Infinity microscope mounting adapter is compatible with Rack and Pinion Mount [#39-357](#) and reduces the thru hole diameter to 58mm. The 90° angle mount, offered in Accessories for Imaging Solutions, allows the mounting of posts at 90° in optical systems. Ring mounts are available for attaching light sources, articulating arms, straight posts, or any 1/4-20 accessory to standard mounting hardware.

Features

90° Angle Mount [#39-355](#) features two 3/4" thru holes at 90° with locking knobs. All Ring Mounts feature 1/4-20 mounting hole, set screw for securing post, or optical component within the inner diameter. Swivel Arm [#03-684](#) features a 0.75" diameter post which accepts rack and pinion focusing mount and allows swivel movement. Infinity Mounting Adapter [#39-358](#) features male and female T-thread to replace 24mm tube section of infinity lens.

Technical Information



Stock No.	A	T	O.D.	I.D.
#54-263	0.375"	0.5"	2.5"	1.5"
#54-264	0.375"	0.5"	1.75"	0.75"
#54-265	0.271"	0.375"	1.25"	0.5"

Diagram of a ring mount showing the outer diameter (OD), inner diameter (ID), and the 1/4-20 Thru hole. The dimensions A and T are also indicated. The units are in inches.