

T-Mount Electrical Shutter



T-Mount Electrical Shutter (#11-153)

Stock **#11-153** **2 In Stock**

⊖ 1 ⊕ C\$1,169⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$1,169.00 each
Qty 5-9	C\$1,035.44 each
Qty 10-25	C\$955.08 each
Need More?	Request Quote

Product Downloads

General

90 **Activation Time (ms):**

50 **Deactivation time (ms):**

Shutter **Function:**

100,000 **Operating Life Cycle:**

Physical & Mechanical Properties

69.0 **Outer Diameter (mm):**

30.0 **Aperture (mm):**

100 **Weight (g):**

16.0 **Extension Length (mm):**

Electrical

90 @25°C **Coil Resistance (Ω):**

±10 **Coil Resistance Tolerance (%):**

7 (full open/close) **Operating Frequency (Hz):**

Hardware & Interface Connectivity

4.5V~5.5VDC **Operating Voltage (V):**

Threading & Mounting

T-Mount **Mount:**

T-Mount **Thread Type:**

M6 x 1.0, 1/4-20 **Compatible Post:**

Environmental & Durability Factors

-10 to +60 **Operating Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

Product Details

- Male and Female C- and T-Threads for Easy Integration
- Simple On/Off Operation with TTL Input
- M6 and 1/4-20 Tapped Holes for Post Mounting

The C and T-Mount Motorized Shutters are ideal for controlling detector exposure or for use as optical choppers. The shutters operate in a normally closed position and open when a 5VDC signal is applied to the input. The C and T-Mount Motorized Shutters have been designed to integrate with other [C and T-Mount components](#) and include M6 and 1/4-20 threaded holes for post mounting to standard metric or English breadboards. To control the opening and closing the shutter, use the On/Off Controller (#87-325) or TTL input. These shutters have male and female C- and T- threads for easy integration.

Note: Shutter leaves are fragile and should not be handled or used with any laser.