

[See all 36 Products in Family](#)

Triple Bandpass Green-Red-NIR Filter M30.5



Stock **#74-603** NEW **1 In Stock**

- 1 + **C\$596^{.40}**

ADD TO CART

Volume Pricing	
Qty 1+	C\$596.40 each
Need More?	Request Quote

Product Downloads

Full Width-Half Max FWHM Range (nm):
20nm, 20nm, 45nm ±10 nm

General

Type:

Triple Bandpass Mounted Imaging Filter

Model Number:

TB550/660/850-30.5

Physical & Mechanical Properties

Outer Diameter (mm):

32.5

Substrate Thickness (mm):

2mm	
Optical Properties	
Green-Red-NIR	Color:
40/20	Surface Quality:
≥85%	Transmission (%):
543-558nm, 653-668nm, 835-865nm	Transmission Wavelength (nm):
Threading & Mounting	
M30.5 x 0.50	Filter Thread:
5.2	Mount Thickness (mm):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

Note: Other filter threads are available upon request.