


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY
DIMENSIONS ARE IN mm [INCHES]

NOTES:

1. OPTIONAL RECESSED SET SCREW INCLUDED

2. APERTURE DIAMETER: 0.8 - 20mm

MAGNIFICATION	1:2	 Edmund Optics®				
WORKING F/#	f/2.8 - f/76					
EFL ELEMENT A/ELEMENT B	30mm/60mm	TITLE C-MOUNT ACHROMAT PAIR 1:2 WITH 30 AND 60mm FOCAL LENGTHS				
COATING	VIS 0°, Ravg ≤ 0.4% @ 425 - 675nm					
DWG NO	87186	MATERIAL	BLACK ANODIZED ALUMINUM	SHEET 1 OF 1	REV	000