




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	512 & 630 $\pm$ 2nm
MINIMUM TRANSMISSION	>90%
BLOCKING	250 - 1100nm
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	HARD COATED
DURABILITY	MIL-C-48497A

**Edmund Optics®**



ALL DIMS IN

mm

TITLE

Ø50mm, 512 & 630nm, DUAL-BAND FILTER

DWG NO

87249

SHEET  
1 OF 1