



NOTES:

- 1. SUBSTRATE:  
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)  
S1: Aluminum w/ Protective Overcoat  
R(AVG)>85% FROM 400-700nm, @ 45° AOI

S2: NONE

3. FINE GRIND SURFACE

4. RoHS COMPLIANT




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	38.18 x 27.00	27.00 x 27.00
COATING APERTURE	38.18 x 27.00	27.00 x 27.00
SURFACE FLATNESS	λ/8	λ/8
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN mm

 Edmund Optics®			
TITLE	30mm, Aluminum Coated, N-BK7 High Tolerance RA Prism		
DWG NO	32552	SHEET 1 OF 1	