

NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <1 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: RAVG ≤0.4% @ 425 - 675nm



5. Rohs Compliant







PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

1 OF 1

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø27.00	Ø27.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED
•	•	•

			Edmund Optics®	
THIRD ANGLE PROJECTION	\$	TITLE	30mm DIA., 4mm THICK, VIS 0° COATE N-BK7 WINDOW	D λ/4
ALL DIMS IN	mm	DWG NO	47521	SHEET