



NOTES:



1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: Enhanced Aluminum (450-650nm)
R(AVG) ≥95% @ 450 - 650nm @ 45°

S2: NONE
3. EDGES SEAMED
4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO				
SURFACE QUALITY	60-40	N/A	 THIRD ANGLE PROJECTION	TITLE	35 x 50mm Enhanced Aluminum, 4-6λ Mirror	
SURFACE FLATNESS	4 - 6λ	N/A		DWG NO	48450	SHEET 1 OF 1
CLEAR APERTURE	33.25 x 47.50	N/A				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED		ALL DIMS IN	mm	