



NOTES:



1. SUBSTRATE MATERIAL:  
N-BK7
2. RoHS COMPLIANT
3. COATING (APPLY ACROSS COATING APERTURE)  
S1:  $R(ABS) \leq 1.5\%$  FROM 750-800nm @ 0° AOI  
 $R(ABS) \leq 1.0\%$  FROM 800-1550nm @ 0° AOI  
 $R(AVG) \leq 0.7\%$  FROM 750-1550nm @ 0° AOI  
S2: NONE

 4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	<div>THIRD ANGLE PROJECTION</div> 				
SHAPE	PLANO	PLANO			25.4mm NIR II 1/4 WAVE FRESNEL RHOMB RETARDER DWL 1064nm		
ANGLE TOL.	±0°3'	±0°3'					
SURFACE QUALITY	20-10	20-10					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	36143	SHEET 1 OF 1