



NOTES:

- 1. SUBSTRATE: FUSED SILICA
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: 532nm HR Coating
 - R(ABS) > 99.8% @ 532nm @ 45° AOI
 - R(AVG) > 99.5% FROM 523-537nm @ 45° AOI
- DAMAGE THRESHOLD
PULSED: 15 J/cm² @ 20ns, 20Hz @ 532nm
CW: 1MW/cm² @ 532nm

3 FINE GRIND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	19.08 x 13.50	Ø13.50
SURFACE FLATNESS	λ/20	λ/20
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION		Edmund Optics®	
ALL DIMS IN		TITLE	15mm 1/20 WAVE, 532nm, HR CTD HYP, HT RA, FS PRISM
mm		DWG NO	37655
			SHEET 1 OF 1