


- NOTES:
- 1. MATERIAL: STAINLESS STEEL AND BLACK ANODIZED ALUMINUM
  - 2. MAX TRAVEL DISTANCE: 25mm
  - 3. RoHS: EXEMPT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO  
CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR  
REFERENCE ONLY

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	25mm TRAVEL, METRIC MICROMETER, SOLID TOP BALL BEARING STAGE	
ALL DIMS IN	in	DWG NO	55282	SHEET 1 OF 1