

## NOTES:

- 1. SUBSTRATE: FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <5 ARCSEC
- 3. COATING (APPLY ACROSS COATING APERTURE):
  - S1 & S2: NIR II (750-1550nm) R(ABS) ≤1.5% @ 750 - 800nm R(ABS) ≤1.0% @ 800 - 1550nm R(AVG) ≤0.7% @ 750 - 1550nm
- 4. WAVELENGTH RANGE: 750 1550nm





## *FOR INFORMATION ONLY:* DO NOT MANUFACTURE PARTS TO THIS DRAWING

## SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2			Edmund Optic	2S®
Shape	PLANO	PLANO				
SURFACE QUALITY	20-10	20-10		TITLE	50mm Dia., 3mm Thick, NIR II Coated λ/10 Fused Silica Window	
TRANSMITTED WAVEFRONT (P-V)	0.10 WAVE	0.10 WAVE				
CLEAR APERTURE	Ø40.00	Ø40.00				0.1557
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN mm	DWG NO	11908	SHEET 1 OF 1