




NOTES:

1. COATING:
S1: MaxiBlack™
THICKNESS (μm) 4 - 6
2. ABSORBANCE: 98%
3. ABRASION RESISTANCE: Moderate
4. HUMIDITY RESISTANCE: MIL-C-48497A
5. OPERATING TEMPERATURE: -40 to 121
6. WAVELENGTH RANGE: 0.3 - 5



DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® **Edmund Optics®**

THIRD ANGLE PROJECTION		TITLE	MaxiBlack Adhesive Polymer Film 200 x 600mm	
		DWG NO	13491	SHEET 1 OF 1