
## NOTES:


MATERIAL:
HOUSING: STAINLESS STEEL
LENS: D-ZK3


2. COATING (APPLY ACROSS CLEAR APERTURE) R(AVG) <0.4% @ 1050 - 1600nm

3. CLEAR APERTURE: 5.00 mm

4. RoHS: COMPLIANT







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

## PARTS TO THIS DRAWING

<b>EO</b> ®	Edmund	Optics®
-------------	--------	---------

THIRD ANGLE PROJECTION		TITLE	1064nm Alignment, 0.16 NA Fiber Collimator w/ SMA Connector	
ALL DIMS IN	mm	DWG NO	64766	SHEET 1 OF 1