




NOTES:

- 1. SUBSTRATE:
POLYMER FILM XP40HT-18 WITH ADHESIVE
- 2. TEMPERTURE RESISTANCE (°C x HOURS):
HEAT: 100 x 1,000
COLD: -40 x 1,000
HUMIDITY: 80 x 90% RH x 1,000
- 3. WAVELENGTH RANGE: 400 -700 nm
- 4. POLARIZATION EFFICIENCY (%): >99.5
- 5. TRANSMISSION (%):
SINGLE: 40 ± 2
PARALLEL: 32.2
CROSSED: <0.005 @ 546nm
- 6. EXTINCTION RATIO: 5000:1
- 7. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	600 x 1000mm HIGH TEMPERTURE LINEAR POLARIZING FILM (XP40HT-18) WITH ADHESIVE
ALL DIMS IN	mm	DWG NO	16020
			SHEET 1 OF 1