

NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <1 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) <0.5% @ 350 - 700nm



5. Rohs Compliant







PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	60-40	60-40	
CLEAR APERTURE	Ø27.00	Ø27.00	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	

			Edmund Optic	;S®
HIRD ANGLE ROJECTION	ϕ	TITLE	30mm DIA., 4mm THICK, VIS-EXT COA λ/4 N-BK7 WINDOW	TED,
all DIMS IN	mm	DWG NO	13299	SHEET 1 OF

30mm DIA., 4mm THICK, VIS-EXT COA λ/4 N-BK7 WINDOW	TED,
10000	SHEFT

1 OF 1