




NOTES:

- 1. SUBSTRATE:
TAC FILM
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: NONE
- 3. PROTECTIVE FILM ON BOTH SURFACES SHOULD BE REMOVED BEFORE USE
- 4. WAVELENGTH RANGE: 300 - 1100 nm
- 5. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	250 x 250mm Light Diffusing Film
ALL DIMS IN	mm	DWG NO	20247
			SHEET 1 OF 1