


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
CENTER WAVELENGTH (nm)	632.80
FULL WIDTH HALF MAX (nm)	0.50
MINIMUM TRANSMISSION (%)	>45
CLEAR APERTURE (mm)	21.00
SUBSTRATE	SODA LIME GLASS & FILTER GLASS

THIRD ANGLE
PROJECTION

ALL DIMS IN

mm

 Edmund Optics®			
TITLE	632.8nm CWL, 0.50 FWHM, 25mm Dia. Ultra Narrow Filter		
DWG NO	21-386	SHEET 5 OF 14	