




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



	VALUE
CENTER WAVELENGTH (nm)	656.30
FULL WIDTH HALF MAX (nm)	0.50
MINIMUM TRANSMISSION (%)	>45
CLEAR APERTURE (mm)	21.00
SUBSTRATE	SODA LIME GLASS & FILTER GLASS

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	656.3nm CWL, 0.50 FWHM, 25mm Dia. Ultra Narrow Filter
ALL DIMS IN	mm	DWG NO	21-387
			SHEET 6 OF 14