

[See all 77 Products in Family](#)

LightPath 354220 | 7.2mm Dia., 0.25 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-118** CLEARANCE **20+ In Stock**

☐ [Other Coating Options](#)

-

1

+

C\$54^{.60}

ADD TO CART

Volume Pricing	
Qty 1+	C\$54.60 each
Need More?	Request Quote

Product Downloads

General	
Thickness: 0.25 (t) (mm) Material: BK7	Compatible Window:
354220	Lightpath Lens Code:
Aspheric Lens	Type:
Collimate or Focus Laser Light	Typical Applications:

Physical & Mechanical Properties	
7.20 ±0.020	Diameter (mm):
5.5	Clear Aperture CA (mm):
4.21	Edge Thickness ET (mm):
5.03 ±0.05	Center Thickness CT (mm):
Protective as needed	Bevel:
6.909	Distance from Window to Lens (D) (mm):


Optical Properties	
11.00 @ 633nm	Effective Focal Length EFL (mm):
0.25	Numerical Aperture NA:
D-ZK3	Substrate: □
±1	Focal Length Tolerance (%):
633	Aspheric Design Wavelength (nm):
BBAR (600-1050nm)	Coating:
R _{abs} <1.0% @ 600 - 1050nm	Coating Specification:
40-20	Surface Quality:
2.00	f/#:
600 - 1050	Wavelength Range (nm):
7.9	Working Distance (mm):
Infinite	Conjugate Distance:
< 0.040	Transmitted Wavefront Error (λ, RMS):

Environmental & Durability Factors	
≤200	Operating Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

Product Details

- Eliminate Spherical Aberration
 - Multiple Coating Options Available
 - Range of Numerical Apertures
- LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information

