

0.3 - 2.5μm, 30W, Volume Absorber, Wireless Power & Energy Detector



0.3 - 2.5μm, 30W, Volume Absorber, Wireless Power & Energy Detector

Stock **#17-211** CLEARANCE **1 In Stock**

-

1

+

C\$2,336²⁷

C\$4,672.54

ADD TO CART

Volume Pricing	
Qty 1+	C\$4,672.54 C\$2,336.27 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General	
Cooling Method:	Heatsink
Maximum Incident Energy Density (J/cm²):	6
Compatible Meters:	Not Required

Physical & Mechanical Properties	
80.6 x50 x61.3	Dimensions (mm):
210	Weight (g):
0.21	Weight (kg):
18	Active Area (mm):
Optical Properties	
300 - 2500	Wavelength Range (nm):
0.3 - 2.5	Wavelength Range (µm):
Sensor	
Volume Absorber	Type of Sensor:
Electrical	
30,000	Maximum Incident Beam Power (mW):
30	Maximum Incident Beam Power (W):
700	Maximum Incident Power Density (W/cm²):
0.7	Maximum Incident Power Density (kW/cm²):
2 mW	Noise Level:
Hardware & Interface Connectivity	
Bluetooth®	Computer Interface:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Bluetooth® Wireless, All-in-One Detector and Meter Solutions
- Monitor Laser Beam Properties via Gentec-EO BLU App (Available for [iOS](#) and [Android](#)) or PC Software
- Long Battery Life of Up to 5 Days with Continuous Use
- Wired [Power and Energy Detectors](#) Also Available

Edmund Optics® Wireless Power and Energy Detectors combine a detector and meter with Bluetooth® technology to provide a convenient, all-in-one solution for laser beam analysis. These detectors are operated by either the Gentec-EO BLU app (available for [iOS](#) and [Android](#)) or via PC with the included Bluetooth receptor and PC-Gentec-EO software. Measurements can be taken up to 30m away from the detector, depending on the physical environment, with the same performance as a wired detector/meter combination. Edmund Optics® Wireless Power and Energy Detectors are compatible with incident beam powers up to 300W and are ideal for labs looking to simplify their laser measurement setups by reducing the number of cables and devices. These detectors have a long battery life of up to 5 days with continuous use and are rechargeable via USB.