

[See all 76 Products in Family](#)

# LightPath 355151 | 3mm Dia., 0.50 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#83-583** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ C\$105<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | C\$105.00 each                |
| Qty 11-49      | C\$94.50 each                 |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

### General

Thickness: 0.25 (t) (mm)  
Material: BK7

Compatible Window:

355151

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:  
Collimate or Focus Laser Light

## Physical & Mechanical Properties

Diameter (mm):  
3.00 ±0.015

Clear Aperture CA (mm):  
2

Edge Thickness ET (mm):  
1.40

Center Thickness CT (mm):  
1.89 ±0.03

Bevel:  
Protective as needed

Distance from Window to Lens (D) (mm):  
0.479

## Optical Properties

Effective Focal Length EFL (mm):  
2.00 @ 780nm

Numerical Aperture NA:  
0.50

Substrate:   
[D-ZLaF52LA](#)

Focal Length Tolerance (%):  
±1

Aspheric Design Wavelength (nm):  
780

Coating:  
BBAR (600-1050nm)

Coating Specification:  
R<sub>abs</sub> <1.0% @ 600 - 1050nm

Surface Quality:  
40-20

f#:  
1.00

Abbe Number (v<sub>d</sub>):  
40.79

Index of Refraction (n<sub>d</sub>):  
1.806

Wavelength Range (nm):  
600 - 1050

Working Distance (mm):  
1.029

Conjugate Distance:  
Infinite

Focal Length Specification Wavelength (nm):  
780.00

Transmitted Wavefront Error (λ, RMS):  
< 0.07

## Material Properties

Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):  
6.9

## Environmental & Durability Factors

Operating Temperature (°C):  
≤200

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 247:  
[Compliant](#)

## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser



## Technical Information

