


## 0.5mW Linear Polarization, Lasos HeNe Laser



Stock #35-205 **1 In Stock**

⊖ 1 ⊕ C\$1,092<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$1,092.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

3R **Laser Class - IEC:**

HeNe **Type of Laser:**

IIIa **Laser Class - CDRH:**

#### Physical & Mechanical Properties

160.00 **Weight (g):**

**Static Alignment:**  
Centered to Outer Cylinder:  $\leq 0.5\text{mm}$   
Parallel to Outer Cylinder:  $\leq 5$

$\leq 0.1$  **Pointing Stability (mrad/°C):**

170.00 **Length (mm):**

35 **Diameter of Laser Head (mm):**

170 **Length of Laser Head (mm):**

## Optical Properties

$\geq 200:1$  **Polarization:**

632.80 **Wavelength (nm):**

0.49 **Beam Diameter (mm):**

$\leq 1.75$  **Beam Divergence (mrad):**

## Electrical

0.5 **Output Power (mW):**

30Hz–10MHz  $\leq 1\%$  **RMS Noise:**

1086.00 **Longitudinal Mode Spacing, Nominal (MHz):**

## Hardware & Interface Connectivity

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#35-221](#)  
Europe: [#35-221](#)  
Japan: Not Available  
Korea: Not Available  
China: Not Available

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Excellent Stability
- Long Lifetime
- Precise Alignment

Lasos Helium-Neon (HeNe) Lasers have a robust mechanical design, excellent beam quality and long service life of up to 30,000 hours. For ease of system integration Lasos HeNe lasers are designed with tough cylindrical housing that precisely aligns with the beam and provides great protection for the laser tube and internal electronics. Each module requires a specially designed turn-key power supply to provide low noise and high stability output. Lasos Helium-Neon (HeNe) Lasers are ideal for a wide range of demanding applications such as spectroscopy, metrology, industrial measurement or confocal laser scanning microscopy. These lasers are offered in both random and linear polarization, in a variety of milli-watt measurements.

**Note:** Power Supply required for operation and sold separately. Requires voltage converter for use in regions with 120V.