

[See all 76 Products in Family](#)

# LightPath 355561 | 15mm Dia., 0.60 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#37-107** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **€119<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>€119.00</b> each
Qty 11-49	<b>€107.10</b> each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

355561 **Lightpath Lens Code:**

Aspheric Lens **Type:**

Collimate or Focus Laser Light **Typical Applications:**

### Physical & Mechanical Properties

15.00 ±0.015	<b>Diameter (mm):</b>
12.5	<b>Clear Aperture CA (mm):</b>
2.56	<b>Edge Thickness ET (mm):</b>
5.38 ±0.05	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>

## Optical Properties

10.00 @ 850nm	<b>Effective Focal Length EFL (mm):</b>
0.60	<b>Numerical Aperture NA:</b>
<a href="#">D-ZLaF52LA</a>	<b>Substrate:</b> <input type="checkbox"/>
±1	<b>Focal Length Tolerance (%):</b>
850	<b>Aspheric Design Wavelength (nm):</b>
BBAR (1050-1600nm)	<b>Coating:</b>
$R_{\text{abs}} < 1.0\%$ @ 1050 - 1600nm	<b>Coating Specification:</b>
60-40	<b>Surface Quality:</b>
0.83	<b>f#:</b>
40.79	<b>Abbe Number (<math>v_d</math>):</b>
1.806	<b>Index of Refraction (<math>n_d</math>):</b>
1050 - 1600	<b>Wavelength Range (nm):</b>
7	<b>Working Distance (mm):</b>
Infinite	<b>Conjugate Distance:</b>
850.00	<b>Focal Length Specification Wavelength (nm):</b>
< 0.40	<b>Transmitted Wavefront Error (<math>\lambda</math>, RMS):</b>

## Material Properties

6.9	<b>Coefficient of Thermal Expansion CTE (<math>10^{-6}/^{\circ}\text{C}</math>):</b>
-----	--

## Environmental & Durability Factors

≤200	<b>Operating Temperature (<math>^{\circ}\text{C}</math>):</b>
------	---

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>


## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



## Technical Information



## Compatible Mounts

---