

[See all 76 Products in Family](#)

# LightPath 354340 | 6.33mm Dia., 0.64 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-162** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ C\$119<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-10	C\$119.00 each
Qty 11-49	C\$107.10 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Thickness: 1.20 (t) (mm)  
Material: K3

Compatible Window:

354340

Lightpath Lens Code:

Aspheric Lens

Type:

Collimate or Focus Laser Light

Typical Applications:

## Physical & Mechanical Properties

6.33 ±0.020 Diameter (mm):

5.1 Clear Aperture CA (mm):

1.48 Edge Thickness ET (mm):

3.10 ±0.03 Center Thickness CT (mm):

Protective as needed Bevel:

1.483 Distance from Window to Lens (D) (mm):

## Optical Properties

4.03 @ 685nm Effective Focal Length EFL (mm):

0.64 Numerical Aperture NA:

D-ZK3 Substrate: □

±1 Focal Length Tolerance (%):

685 Aspheric Design Wavelength (nm):

BBAR (600-1050nm) Coating:

R<sub>abs</sub> <1.0% @ 600 - 1050nm Coating Specification:

40-20 Surface Quality:

0.78 f#:

60.88 Abbe Number (v<sub>d</sub>):

1.586 Index of Refraction (n<sub>d</sub>):

600 - 1050 Wavelength Range (nm):

2.68 Working Distance (mm):

Infinite Conjugate Distance:

685.00 Focal Length Specification Wavelength (nm):

< 0.08 Transmitted Wavefront Error (λ, RMS):

## Material Properties

7.6 Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):

## Environmental & Durability Factors

≤200 Operating Temperature (°C):

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser



## Technical Information

