

10 mW, 1550nm Alignment Laser Diode



Red and IR Alignment Laser Diode

Stock #29-129 **20+ In Stock**

C\$1,687⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-9 | C\$1,687.00 each |
| Qty 10+ | C\$1,518.30 each |
| Need More? | Request Quote |

Product Downloads



General

IIIb **Laser Class - CDRH:**

Physical & Mechanical Properties

36.00 **Length (mm):**

Optical Properties

1,550.00 **Wavelength (nm):**

| | |
|---|------------------------------------|
| ±10 | Wavelength Tolerance (nm): |
| 3.5 typical | Beam Diameter (mm): |
| <1.0 | Beam Divergence (mrad): |
| Infrared | Color: |
| Electrical | |
| 10 | Output Power (mW): |
| 0 - 10 | Modulation Frequency (kHz): |
| Hardware & Interface Connectivity | |
| 5 | Operating Voltage (V): |
| Power Supply: Power Supply Required and Sold Separately: USA: #73-818 Europe: #73-818 Japan: #13-640 Korea: #33-770 China: #73-818 | |
| Environmental & Durability Factors | |
| 10 to 35 | Operating Temperature (°C): |
| Regulatory Compliance | |
| View | Certificate of Conformance: |

Product Details

- Focus Adjustable
- TTL Modulation up to 10kHz
- 635nm, 780nm, 808nm, 850nm, and 980nm Wavelength Options

Red and IR Alignment Laser Diodes are available in output powers from 1 to 100mW at 635nm, 780nm, 808nm, 850nm, and 980nm wavelengths. These low cost laser diode modules combine drive electronics and beam collimating optics, making them ideal for OEM integration applications. Red and IR Alignment Laser Diodes feature TTL Modulation up to 10kHz and are best utilized in alignment applications or systems with simple detectors.

Note: Power supply and mounting bracket are sold separately.