

**TECHSPEC® 10mm 532nm, Laser Line Polarizing Cube Beamsplitter**



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#48-571** **20+ In Stock**

⊖ 1 ⊕ C\$383<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$383.60 each
Qty 6-25	C\$310.80 each
Qty 26-99	C\$281.40 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Linear Polarizer **Type:**

**Physical & Mechanical Properties**

Protective as needed **Bevel:**

90.00 **Clear Aperture (%):**

Cube **Construction:**

10.0 x 10.0 x 10.0 ±0.1 **Dimensions (mm):**

## Optical Properties

±3 **Beam Deviation (arcmin):**

$R_{\text{abs}} < 0.25\%$  @ 532nm **Coating Specification:**

532 **Design Wavelength DWL (nm):**

1000:1 **Extinction Ratio:**

>95 **P-Polarization Transmission (%):**

>99.5 **S-Polarization Reflection (%):**

**Substrate:**  [N-BK7](#)

40-20 **Surface Quality:**

1.25 **Power (fringes) @ 632.8nm:**

0.25 **Irregularity (fringes) @ 632.8nm:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**


[Compliant](#) **Reach 219:**

[View](#) **Certificate of Conformance:**

## Product Details

- Designed for Common Diode, Gas, and Solid State Lasers
- Reflects S-Polarized Light, Transmits P-Polarized Light
- High Extinction Ratio

TECHSPEC® Laser Line Polarizing Cube Beamsplitters split randomly polarized beams into two orthogonal, linearly polarized components. S-polarized light is reflected at a 90° angle, while P-polarized light is transmitted. The beamsplitters consist of a pair of precision [right angle prisms](#) cemented together to minimize transmitted wavefront distortion, and to provide excellent parallelism between incoming and transmitted beams. TECHSPEC® Laser Line Polarizing Cube Beamsplitters are designed for many common laser wavelengths and have a high extinction ratio. These beamsplitters are designed for common diode, gas, and solid-state laser applications.



**LASER OPTICS** MADE BY EDMUND OPTICS® [LEARN MORE](#)

## Technical Information

