

[See all 5 Products in Family](#)

# 10mm Dia. x 10mm EFL Arton Plastic Asphere, Coated



Stock #90-323 20+ In Stock

-

1

+

C\$92<sup>.40</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | C\$92.40 each                 |
| Qty 11-49      | C\$77.00 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Aspheric Lens

Physical & Mechanical Properties

Diameter (mm):

10.00

Clear Aperture CA (mm):

8.00

Edge Thickness ET (mm):

3.1


|                                      |                                  |
|--------------------------------------|----------------------------------|
| Protective as needed                 | Bevel:                           |
| 8.28                                 | Flange Distance (mm):            |
| Optical Properties                   |                                  |
| 10.00 ±0.2                           | Effective Focal Length EFL (mm): |
| 0.40                                 | Numerical Aperture NA:           |
| 8.28                                 | Back Focal Length BFL (mm):      |
| Arton Plastic                        | Substrate: □                     |
| BBAR (650-850nm)                     | Coating:                         |
| R <sub>abs</sub> <1.0% @ 650 - 850nm | Coating Specification:           |
| 1.25                                 | f/#:                             |
| 650 - 850                            | Wavelength Range (nm):           |
| Infinite                             | Conjugate Distance:              |
| Regulatory Compliance                |                                  |
| <a href="#">View</a>                 | Certificate of Conformance:      |

## Product Details

- Superior Durability for Harsh Environments
- High Heat Resistance
- Low Water Absorbency

Arton® Plastic Aspheric Lenses are ideal alternatives to PMMA or polycarbonate plastic aspheric lenses for weight sensitive, harsh environment applications. Typical plastic substrates degrade in performance in hot or humid environments. Arton®, a polyolefin thermoplastic plastic substrate, maintains plastic's high translucency and low birefringence, while featuring increased heat resistance and decreased water absorbency.

## Technical Information



## Compatible Mounts