

[See all 2 Products in Family](#)

10mm Dia. x 18mm FL, 650-1000nm AR Coated, Gradium Lens

See More by [Lightpath®](#)



Stock **#47-600** CLEARANCE **9 In Stock**

-

1

+

C\$350⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$350.00 each
Need More?	Request Quote

Product Downloads

General

Gradient Index Lens

Type:

Physical & Mechanical Properties

10.00 ±0.25

Diameter (mm):

1.00

Centering (arcmin):

9.00

Clear Aperture CA (mm):

2.50	Center Thickness CT (mm):
Optical Properties	
18.00 @ 546nm	Effective Focal Length EFL (mm):
0.25	Numerical Aperture NA:
16.52	Back Focal Length BFL (mm):
±1	Focal Length Tolerance (%):
BBAR (650-1000nm)	Coating:
R _{avg} <0.5% @ 650 - 1000nm	Coating Specification:
40-20	Surface Quality:
2.00	f/#:
650 - 1000	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

Product Details

- Aspheric Performance
- Smaller Focused Spot Size
- Reduced Spherical Aberration

GRADIUM® lenses utilize advances in the manufacturing of axial gradient glass to improve lens performance. The process turns a glass of several SF layers into a single glass with a gradually changing index. The index may change by as much as 0.15 from the front surface to the back surface. This change in index allows for correction of system aberrations, especially spherical, yielding better images in infinite/finite imaging applications. GRADIUM® lenses are ideal for laser focusing applications, providing smaller spot sizes compared to the standard PCX counterpart. Two broadband antireflection coating options are available that cover a large range of visible and near-infrared laser wavelengths. For OEM and high volume coating options, please contact our [Applications Engineering Department](#) to discuss your requirements.

Technical Information

