

10mm FL, 532nm, Visible Metalens Plate



Stock #86-929 NEW CONTACT US

-
1
+
C\$1,050⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	C\$1,050.00 each
Qty 10+	C\$945.00 each
Need More?	Request Quote

Product Downloads

General

Note:
Black absorptive aperture applied to metasurface

Physical & Mechanical Properties

Dimensional Tolerance (mm):
+/-0.2

Thickness (mm):
0.70 ±0.07

Outer Dimensions (mm):
20.0 x 20.0

Inner Diameter (mm):

Optical Properties

10.00 ±2% **Effective Focal Length EFL (mm):**

Eagle XG **Substrate:** □

0.20 **Numerical Aperture NA:**

Broadband 420-670nm AR Coating, backside
Protective Overcoat, frontside **Coating:**

Broadband 420-670nm AR-Coating (Back surface only)
 $R_{\text{abs}} \leq 1\%$ from 420-670nm
 $R_{\text{avg}} \leq 0.4\%$ from 420-670nm **Coating Specification:**

532 **Design Wavelength DWL (nm):**

1.5198 (435.8 nm), 1.5078 (643.8 nm) **Index of Refraction (n_d):**

80 **Transmission (%):**

Material Properties

31.7 x 10⁻⁷/°C (0-300°C) **Thermal Expansion:**

Environmental & Durability Factors

>= 200C, 1000hrs **Environmental Durability:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Flat, Space Saving Alternative to Traditional Lenses
- Nanostructure Design Enables Efficient Manipulation of Light
- Compact 0.7mm Thickness for Easy Integration into a Variety of Applications

Visible Metalens Plates are designed with an innovative nanostructure design to manipulate and focus light, offering a highly compact and high-performance alternative to traditional curved lenses. Featuring ultra-thin Eagle XG substrates, these lens plates are available for 532nm and 632nm design wavelengths in a range of focal lengths. These metalenses are available in a single lens construction, where an individual metalens is centered on the plate and surrounded by an absorptive aperture to reduce stray light, or an array construction, where one of each of the four smaller Metalenses are arranged on a single plate for versatility. Visible Metalens Plates are ideal for low SWaP, LIDAR, imaging, and beam shaping applications.

Note: The Metalens surface is very delicate, and contact should be avoided during cleaning and handling. Visible Metalens Plates should be cleaned only using compressed air.