

[See all 4 Products in Family](#)

10" x 18", Anti-Static Cleaning Cloths



10" x 18", Anti-Static Cleaning Cloths (Assorted Colors - Color May Vary)

Stock **#57-604** **5 In Stock**

-

1

+

C\$31⁵⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$31.50 each
Qty 6-24	C\$28.35 each
Qty 25-99	C\$24.50 each
Need More?	Request Quote

Product Downloads

General	
Anti-Static	Type:
Physical & Mechanical Properties	
10 x 18	Dimensions (inches):
Regulatory Compliance	

Product Details

- Photo-Clear® and Anti-Static Options
- Anti-Static Design Dissipates Static Charges
- Photo-Clear® Design Efficiently Removes Debris and Moisture

Cleaning Cloths are composed of extremely durable, tightly woven poly/nylon microfibers. The microfibers effectively cut through dirt and lift oil and moisture from the lens surface. It differs from most cloths which move the dirt and oils around instead of removing them. The anti-static micro-fiber cloths utilizes stripes of effective conductive fibers knit every 1/8" that dissipate or drain off static charges. Cleaning Cloths have hundreds of thousands of small pockets in the cloth that aggressively capture the dust and dirt. The thick, soft cloths are completely non-abrasive.