


[See all 7 Products in Family](#)

10X Mitutoyo Telecentric Objective

See More by [Mitutoyo](#)



3X (#56-985) & 5X (#56-986)



Stock **#56-987** **2 In Stock**

C\$2,121⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,121.00 each
Need More?	Request Quote

Product Downloads

General

375-039 **Model Number:**

Microscope Objective **Type:**

Finite Conjugate **Style:**

Manufacturer:

Note:

Image is formed 280mm from specimen (170mm from the mounting flange)

Physical & Mechanical Properties

Length (mm):

59.00

Length excluding Threads (mm):

59.00

Maximum Diameter (mm):

30

Weight (g):

95

Optical Properties

Horizontal Field of View, 1/2" Sensor:

0.64mm

Horizontal Field of View, 2/3" Sensor:

0.88mm

Focal Length FL (mm):

17.50

Aperture (f/#):

NA0.21

Magnification:

10X

Numerical Aperture NA:

0.21

Resolving Power (μm):

1.31

Depth of Field (μm):

6.20

Field of View, 24 Diameter Field Eyepiece (mm):

2.4

Field of View, 18 Diameter Field Eyepiece (mm):

1.8

Working Distance (mm):

51

Wavelength Range (nm):

435 - 655

Parfocal Length (mm):

110

Immersion Liquid:

N/A

Maximum Image Circle (mm):

11.00

Sensor

Maximum Sensor Format:

2/3"

Threading & Mounting

Mount:

M26 x 36 TPI

Mounting Threads:

M26 x 36 TPI

Environmental & Durability FactorsOperating Temperature ($^{\circ}\text{C}$):

+5 to +40

Operating Humidity:

20 - 80%

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Contains SVHC\(s\)](#)**Product Details**

- Long Working Distances Allow for Integration into Machine Vision Measurement Systems
- Compact Design and Long Parfocal Length Simplifies Mounting
- [Tube](#) Available for Use with C-Mount Cameras
- Aluminum Alloy Housing

Mitutoyo Telecentric Objectives are ideal for high-resolution, high power machine vision measurement and optical gauging systems. With powers up to 100X, these objectives can be used for semiconductor production and inspection, and in metrology, quality assurance, and R&D laboratories. These objectives are constructed of an aluminum alloy housing. Mitutoyo Telecentric Objectives have a compact design and a long parfocal length that simplifies mounting. They are easily integrated into C-Mount imaging systems with our Mitutoyo C-Mount Camera Tube [#56-992](#).

Edmund Optics is the main source for Mitutoyo Objectives. Place your orders now for these in demand quality products.

Technical Information

Magnification	A	B	C	D	E	Stock No.
1X	49	10	16.5	31.5	31.5	#56-984
3X	33	10	18	25	28	#56-985
5X	49	10	17	25	28	#56-986
10X	59	10	14.5	30	30	#56-987
20X	90	14.5	23	33	39	#87-228
50X	97	14.7	23	33	39	#87-229
100X	104	14.1	23	33	39	#87-230

