

[See all 2 Products in Family](#)

**TECHSPEC® 12.7 x 50.8mm EFL 90° VIS Coated Glass Off-Axis Parabolic Mirror**



High Performance Fused Silica Off-Axis Parabolic (OAP) Mirrors



Stock #18-670 **14 In Stock**

- 1 + C\$1,197<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$1,197.00 each
Qty 6-25	C\$1,079.40 each
Qty 26-50	C\$1,019.20 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Off-Axis Parabolic Mirror **Type:**

**Physical & Mechanical Properties**

50.80 **Y Offset (mm):**

12.70 +0/-0.10	<b>Diameter (mm):</b>
90	<b>Clear Aperture (%):</b>
<10 RMS	<b>Surface Roughness (Å):</b>
<b>Optical Properties</b>	
MS	<b>Coating:</b>
90	<b>Off-Set Angle (°):</b>
400 - 750	<b>Wavelength Range (nm):</b>
50.80	<b>Effective Focal Length EFL (mm):</b>
<a href="#">UV Fused Silica</a>	<b>Substrate:</b> <input type="checkbox"/>
<b>Coating Specification:</b> R <sub>avg</sub> >98% @ 400-750nm (0°-45° AOI for All Polarizations) R <sub>avg</sub> >99% @ 400-750nm (0°-45° AOI for S-Polarization)	
±1	<b>Focal Length Tolerance (%):</b>
25.4	<b>Parent Focal Length PFL (mm):</b>
λ/8 @ 632.8nm	<b>Surface Figure, RMS:</b>
40-20	<b>Surface Quality:</b>
<b>Damage Threshold, By Design:</b> <input type="checkbox"/> 0.5J/cm <sup>2</sup> , 20ns, 20Hz @ 532nm	
λ/4 @ 632.8nm	<b>Reflected Wavefront, RMS:</b>

<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 235:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- High Quality Fused Silica Substrate
- <10Å Surface Roughness for Low Scatter
- 90° Offset Angle for Easy Integration

TECHSPEC® High Performance Fused Silica Off-Axis Parabolic (OAP) Mirrors feature a surface roughness of less than 10Å which is the lowest scatter available in an off-the-shelf solution. Featuring a fused silica substrate, these low scatter alternatives perform better in the UV wavelength range than traditional metallic substrate OAPs. TECHSPEC® High Performance Fused Silica Off-Axis Parabolic (OAP) Mirrors are ideal for Schlieren, MTF, and Czerny-Turner and Littrow spectrometer systems due to their low scattering.

**Note:** Uncoated options require a coating for use. Contact us for a custom coating quote for your specific wavelength.