


[See all 3 Products in Family](#)

# 12.7mm Dia. 5°, 800nm Highly-Dispersive Ultrafast Mirror

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) 800nm Highly-Dispersive Ultrafast Mirrors



Stock **#12-330** **9 In Stock**

C\$635<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-3	C\$635.60 each
Qty 4-7	C\$562.80 each
Qty 8+	C\$498.40 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

**Type:**  
 Laser Mrror

**Model Number:**  
 HD15

## Physical & Mechanical Properties

Wedge Angle (arcmin):  
10 ±5

Clear Aperture (%):  
80

Back Surface:  
Commercial Polish

Diameter (mm):  
12.70 +0.0/-0.1

Thickness (mm):  
6.35 ±0.20

## Optical Properties

Reflection at DWL (%):  
>99.9% (typical, p-polarization)

Coating Specification:  
R<sub>avg</sub> >99.8%, GDD = -1300 fs<sup>2</sup> @ 780 - 830nm (p-polarization)  
R<sub>abs</sub> >99.9% @ 800nm (typical, p-polarization)

GDD Specification:  
-1300fs<sup>2</sup> @ 780 - 830nm

Wavelength Range (nm):  
780 - 830

Irregularity (P-V) @ 632.8nm:  
λ/10

Coating Type:  
Dielectric

Coating:  
Ultrafast (780-830nm)

Design Wavelength DWL (nm):  
800

Angle of Incidence (°):  
5

Substrate:   
[Fused Silica](#) (Corning 7980)

Damage Threshold, By Design:   
0.3 J/cm<sup>2</sup> @ 800nm, 50fs, 1kHz, 100µm Beam Diameter

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 235:  
[Compliant](#)

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Reflection >99.8% (P-polarization) at 720 – 840nm or 780 – 830nm
- Low Group Delay Dispersion at 5° or 20° AOIs
- Ideal for Pulse Compression of Ti:sapphire Ultrafast Lasers
- [Low GDD Mirrors](#) Also Available

UltraFast Innovations (UFI) 780 and 800nm Highly-Dispersive Ultrafast Mirrors feature an optimized multilayer ultrafast chirped coating based on dispersive optical interference that provides a low group delay dispersion (GDD) and high reflectance. These ultrafast mirrors provide GDDs as low as -1300fs<sup>2</sup> and greater than 99.8% reflectivity for p-polarization. The highly-dispersive design of these ultrafast mirrors offers control of third and higher order dispersions, and provides high beam stability at either 5° or 20° angle of incidence. UltraFast Innovations (UFI) 780 and 800nm Highly-Dispersive Ultrafast Mirrors are ideal for pulse compression and dispersion compensation of ultrafast pulses, such as Ti:sapphire lasers. Standard imperial sizes are available, featuring fused silica substrates.

## Technical Information



## Compatible Mounts

---

;