

# LightPath 355230 | 1310nm Alignment, 0.55 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #64-792 CLEARANCE  In Stock

⊖ 1 ⊕

**C\$165.13**

**ADD TO CART**

Qty 1+

C\$165.13

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Effective Focal Length EFL (mm):**  
4.51 @ 780nm

**Numerical Aperture NA:**  
0.55

**Substrate:**   
[D-ZLaF52LA](#)

**Coating:**  
BBAR (1050-1600nm)

**Coating Specification:**  
R<sub>abs</sub> <1.0% @ 1050 - 1600nm

**Surface Quality:**  
40-20

**Clear Aperture CA (mm):**  
4.95

**f#:**  
0.91

**Bevel:**  
Protective bevel as needed

**Connector:**  
SMA

**Construction:**  
304L Stainless Steel Housing

**Housing Diameter (mm):**  
11.00

**Housing Length (mm):**  
9.6

**Lightpath Lens Code:**  
355230

**Mount:**  
M11 x0.5

**Type:**  
Fiber Collimator

**Wavelength Range (nm):**  
1050 - 1600

**Conjugate Distance:**  
Infinite

**Lens Included:**  
[#87-155](#)

**Alignment Wavelength (nm):**  
1310

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 233:**  
[Compliant](#)

---