

[See all 8 Products in Family](#)

## 70mm., 15mm Travel, Compact Motorized Linear Stage, Metric



70mm., 15mm Travel, Compact Motorized Linear Stage (Front)



Stock **#23-923** **3 In Stock**

⊖ 1 ⊕ C\$1,071<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	C\$1,071.00 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

Metric **Type:**

**Note:**  
Two integrated, adjustable limit switches  
Controller Required: [#23-931](#)

**Type of Motor:**

## Physical & Mechanical Properties

Linear (X)	Type of Movement:
Ball Bearing	Guide System:
70 x 107	Stage Size (mm):
15	Travel (mm):
5	Accuracy ( $\mu\text{m}$ ):
50	Backlash ( $\mu\text{m}$ ):
Aluminum, 3D Printed Plastic	Construction:
33	Height (mm):
1	Load Capacity (kg):
22	Parallelism ( $\mu\text{m}$ ):
3	Repeatability ( $\mu\text{m}$ ):
40	Speed (mm/s):
0.615	Weight (kg):
1.25	Min. Incremental Movement ( $\mu\text{m}$ ):

## Optical Properties

5	Resolution ( $\mu\text{m}$ ):
---	-------------------------------

## Electrical

600	Maximum Operating Current (mA):
-----	---------------------------------

## Hardware & Interface Connectivity

Lead Screw	Type of Drive:
USB-C	Control Interface:
USB-C	Computer Interface:

## Threading & Mounting

(9) M6 x 1.0, (4) M3 x 0.5, (8) M2 x 0.4	Mounting Threads:
--	-------------------

## Environmental & Durability Factors

10-40	Operating Temperature ( $^{\circ}\text{C}$ ):
-------	---

## Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

## Product Details

- Compact Footprint and Economic Price Point
- Light-weight Housing with Durable Stage Platform
- Compatible with [TECHSPEC Stages](#)
- Use Power Supply [#21-075](#) to Power Controller [#23-931](#)

Compact Motorized Linear Stages are a cost-effective solution for motorized linear adjustment within an optical system. These stages feature an anodized aluminum stage platform for precision mounting, with a Selective Laser Sintering (SLS) 3D printed plastic housing for a lightweight but durable construction. The compact overall footprint maximizes space efficiency to add motorization to space constrained systems. Compact Motorized Linear Stages share the same hole patterns as our [TECHSPEC stages](#), making them an ideal lab bench component for motorized system building. Requires a Controller, [#23-931](#), which can be easily connected via an included 1m USB-C to USB-A cable.

