

TECHSPEC® 16mm FL, Liquid Lens M12 Lens



TECHSPEC® Liquid Lens M12 Imaging Lenses



+1

Stock #37-524 **20+ In Stock**

⊖ 1 ⊕ C\$707⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$707.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Series:

LL M12 Series

Note:

Separate driver not included. Electronic development kit #28-773 recommended. When using a Maxim driver board (#12-247, #12-248, or #17-172) the jumper at ST2 **must** be removed before use to ensure optimal performance and product lifetime.

Watch this [video](#) for more information.

M12 Imaging Lens **Type:**

Integrated Liquid Lens Model:
Corning® Varioptic® A-39N0

No **IR Cut Filter:**

Liquid Lens Focusable **Special Type of Lens:**

Physical & Mechanical Properties

Fixed **Iris Option:**

31.60 **Length (mm):**

27 **Maximum Diameter (mm):**

27 **Outer Diameter (mm):**

7.7 **Maximum Rear Protrusion (mm):**

14.025 **Flange Distance (mm):**

Optical Properties

Horizontal Field of View @ Max Sensor Format:
109.4mm - 25.5°

Field of View at Max Sensor Format:
Horizontal: 109mm - 25.4°
Vertical: 81.7mm - 19.2°
Diagonal: 136.2mm - 31.5°

Horizontal Field of View, 1/1.8" Sensor:
109.4mm - 25.5°

Horizontal Field of View, 1/2" Sensor:
97.2mm - 22.7°

Horizontal Field of View, 1/2.5" Sensor:
88.102mm - 20.6°

Horizontal Field of View, 1/3" Sensor:
70.9mm - 17.1°

Horizontal Field of View, 1/4" Sensor:
54.7mm - 12.9°

9.00 **Maximum Image Circle (mm):**

0.0137 **Numerical Aperture NA, Object Side:**

6(5) **Number of Elements (Groups):**

400 - 700 **Wavelength Range (nm):**

16.00 **Focal Length FL (mm):**

220 - ∞ **Working Distance (mm):**

f/2.4 **Aperture (f/#):**

-0.33 @ Full Field **Distortion (%):**

λ/4 MgF₂ @ 550nm **Coating Specification:**

18.21 **Entrance Pupil Position (mm):**

24.98 **Object Space Principal Plane (mm):**

-8.78 **Image Space Principal Plane (mm):**

-0.33 **Maximum Distortion (%):**

-20.62 **Exit Pupil Position (mm):**

VIS **Lens Wavelength Range:**

Sensor

1/1.8" **Maximum Sensor Format:**

2.74

Pixel Size (µm):

Threading & Mounting

N/A	Filter Thread:
S-Mount (M12 x0.5)	Mount:

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Up to 1/1.8", S-Mount Lens
- Up to 5 MegaPixels, 2.8µm Pixel Size Sensors
- Liquid Lens Provides Quick Autofocus
- 6mm to 16mm Focal Length

TECHSPEC® Liquid Lens M12 Lenses feature a high-resolution f/2.4 optical design with an integrated liquid lens, allowing for fast electronic focus, superior image performance, and a quick autofocus solution. When combined with appropriate camera and software, the focus tunable liquid lens provides the active focus control needed to achieve an autofocus solution. The high light throughput f/2.4 aperture is ideal for high-speed machine vision applications. TECHSPEC® Liquid Lens M12 Lenses incorporate a 2-piece housing design for easy access and replacement of the included liquid lens. The liquid lens can also be rotated 180° inside the imaging lens for quickly accessing the liquid lens control cable.

These lenses won the [2nd place 2019 Inspect Award](#).

Note: Driver and software are required for operation and must be purchased separately unless camera in use has liquid lens control capability. Various drivers and software are included in the Electronics Development Kit ([#28-773](#)). Individual drivers can also be purchased separately if software is not needed ([#12-247](#) or [#12-248](#)).

Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- [Blue Series M12 Lenses](#): High resolution finite conjugate designs optimized for machine vision working distances.
- [Rugged Blue Series M12 Lenses: Stabilized ruggedization](#) versions of our Blue Series M12 Lenses, utilizing the same optics.
- [Green Series M12 Lenses](#): Finite conjugate designs optimized for machine vision working distances.
- [Red Series M12 Lenses](#): Infinite conjugate designs optimized for high resolution performance out to infinity.
- [HEO Series M12 Lenses](#): Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- Liquid Lens M12 Lenses: Integrated liquid lens for fast electronic focus.