

[See all 4 Products in Family](#)

16oz. Resin, 2oz. Hardener, Electrical Grade Epolite FH-5313 Epoxy



Stock #17-461 **1 In Stock**

- 1 + C\$896⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$896.00 each
Need More?	Request Quote

Product Downloads

General

Bottle	Type:
16 (Resin) 2 (Hardener)	Size (oz):
5 hours @5°C 1 hour @50°C	Cure Time:
12 months after opening	Shelf Life:

Material Properties

1970 **Viscosity (cps):**

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)

Product Details

- Two Part Epoxy
- Optical and Electrical Grade
- Cures at Room Temperature

Epolite FH-5313 Epoxy is a two-part optical and electrical grade epoxy that cures at room temperature. This epoxy comes with either an optical hardener, for optical applications requiring high transmission through the cured epoxy, or an electrical hardener, for electrical applications such as potting and encapsulation. Both epoxies feature low outgassing, high mechanical strength, excellent chemical resistance, and are designed for continuous operation at temperatures up to 93°C. Epolite FH-5313 Epoxy is ideal for bonding glass, metal, or plastic and is available in either premeasured 6g packs, or kits containing 16 oz. of resin and 2 oz. of hardener with 6 droppers included for application.

;