

TECHSPEC® 19.1mm Dia., 6.35mm Thick, 532nm, λ/10 Fused Silica Window



TECHSPEC λ/10 Laser Line Coated Windows

Stock **#38-968** **8 In Stock**

1 C\$221⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$221.20 each
Qty 6-25	C\$177.80 each
Qty 26-49	C\$166.60 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Laser Line Window

Type:

Type of Window:

Glass

Physical & Mechanical Properties

17.19 **Clear Aperture CA (mm):**

19.10 +0.00/-0.10 **Diameter (mm):**

6.35 ±0.20 **Thickness (mm):**

<3 **Parallelism (arcmin):**

Protective as needed **Bevel:**

90 **Clear Aperture (%):**

Fine Ground **Edges:**

Optical Properties

0 **Angle of Incidence (°):**

Laser V-Coat (532nm) **Coating:**

532 **Design Wavelength DWL (nm):**

Fused Silica (Corning 7980) **Substrate:**

1.458 **Index of Refraction (n_d):**

10-5 **Surface Quality:**

67.8 **Abbe Number (v_d):**

R_{abs} <0.25% @ 532nm **Coating Specification:**

λ/10 **Surface Flatness (P-V):**

10 J/cm² @ 532nm, 20ns, 20Hz **Damage Threshold, By Design:**

10 J/cm² @ 532nm, 20ns, 20Hz **Damage Threshold, Pulsed:**

Material Properties

7980 0F **Fused Silica Grade:**

Regulatory Compliance

Compliant **RoHS 2015:**

Compliant **Reach 209:**




View **Certificate of Conformance:**

PRODUCT DETAILS

- 10-5 Surface Quality
- Damage Thresholds at Design Wavelengths
- Diameters from 12.5 to 76.2mm Available
- [Uncoated Substrates Available](#)

TECHSPEC® λ/10 Laser Line Coated Windows are designed for direct integration into laser applications. This robust product family features common imperial sizes, many of which offer multiple thickness options. Anti-reflection coatings are available at common laser wavelengths, minimizing surface reflection for optimal system transmission. TECHSPEC λ/10 Laser Line Coated Windows provide laser grade specifications including λ/10 surface flatness, 10-5 surface quality, and <3 arcmin parallelism. These windows are ideal for industrial laser applications ranging from protective coverings to separating various environments.

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS