

Photometrics Iris 15 PCIe Camera, 1T-01-IRIS-15-PCIE-M-16-C



#90-391 Photometrics Iris 15 PCIe Camera



Stock #90-391 NEW 1 In Stock

-

1

+

 C\$22,750⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$22,750.00 each
Need More?	Request Quote

Product Downloads

Monochrome		Spectrum:
General		
Monochrome Camera		Type:
1T-01-IRIS-15-PCIE-M-16-C	Model Number:	
Teledyne Photometrics	Manufacturer:	

Iris		Camera Series:
		Note:
Includes: PCI Express (PCIe) interface card PCI Express data cable 12V/ 5A power supply with international power cord set (2) Single-line MMCX trigger cables USB memory device containing PVCAM library and drivers Quick installation guide		
Physical & Mechanical Properties		
78 x 78 x 118	Dimensions (mm):	
680	Weight (g):	
Full	Housing:	
Optical Properties		
400 - 1000	Wavelength Range (nm):	
Sensor		
1.5"	Sensor Format:	
14.90	Resolution (Megapixels):	
30.00	Frame Rate (fps):	
5,056 x 2,960	Pixels (H x V):	
21.49 x 12.58	Sensing Area, H x V (mm):	
GPixel Gsense 5130	Imaging Sensor:	
Progressive Scan CMOS	Type of Sensor:	
Rolling	Shutter Type:	
16 bit	Pixel Depth:	
12μs- 10s	Exposure Time:	
78	Dynamic Range (dB):	
Hardware & Interface Connectivity		
PCIe	Connector:	
GPIO with #90-400	Power Supply:	
1 configurable input, 3 configurable outputs	GPIOs:	
Hardware Trigger (GPIO) or Software Trigger	Synchronization:	
Back Panel	Interface Port Orientation:	
BNC	GPIO Connector Type:	
Threading & Mounting		
F-Mount	Mount:	
(1) ¼–20 thread per side	Mounting Threads:	
Environmental & Durability Factors		
0 to 30	Operating Temperature (°C):	
–20 to 60	Storage Temperature (°C):	
Regulatory Compliance		
Exempt	RoHS 2015:	


View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- High Resolution Imaging Even at Low Magnifications
- Small 4.25µm Pixels Across Large Arrays
- Advanced Triggering
- Scientific Cameras for High Sensitivity Microscopy Applications



Teledyne Photometrics Iris PCIe Cameras utilize high-resolution sCMOS sensors with 4.25 µm pixels and large sensor formats. This enables precise imaging at low magnifications by maximizing spatial sampling across wide fields of view without sacrificing sensitivity or frame rate. These cameras also feature programmable scan and readout modes that allow precise control of exposure timing and sensor readout direction. Additionally, their advanced triggering capabilities enable seamless synchronization with external devices for high-speed or time-critical imaging applications. Teledyne Photometrics Iris PCIe Cameras are available in C-Mount and F-Mount configurations and are ideal for light-sheet microscopy, live-cell fluorescence, or imaging large samples at high resolutions. These cameras include Teledyne's proprietary-designed software platforms, Beacon and PViCAM, for optimizing camera performance and ease of system integration.



High Resolution

The small, 4.25 µm pixels provide highly detailed images across the imaging plane, which allows for the highest resolution when using lower magnification objectives.

Large Field of View


The larger format 25 mm sensor of the Iris 15 is designed to increase throughput, maximize the amount of data captured and take full advantage of new, larger field of view microscopes.

Compact Form Factor

The Iris 9 (76 x 76 x 88 mm) and Iris 15 (78 x 78 x 108 mm) cameras feature optimized cooling for the size, ideal for integration into new or existing configurations.

Advanced Triggering

Programmable Scan Mode provides increased control over the rolling shutter exposure and read-out functionality of CMOS sensors by providing access to the sensor timing settings to allow optimization around applications that require control over the line time.



Superior Background Quality

The Iris Family feature Pattern Noise Reduction Technology and Correlated Noise Reduction Technology to ensure that they deliver clean, pattern-free images with minimal pixel defects, delivering improved image quality in low light conditions.