


Differential Micrometer Drive Fiber Alignment Mount



2-Axis Fiber Alignment Mount w/ Micrometer Kinematic Movement , #55-477

Stock **#55-477** **20+ In Stock**

⊖ 1 ⊕ C\$749⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$749.00 each
Need More?	Request Quote

Product Downloads

General

Adjustable - Linear (XY) **Type:**

Fiber Connector **Type of Optics:**

Physical & Mechanical Properties

Black Anodized Aluminum **Construction:**

±1.5 **Linear Travel (mm):**

Linear Travel Resolution (μm):

2.5

Electrical

Fiber Connection:

FC

Hardware & Interface Connectivity

Type of Drive:

Differential Micrometer

Threading & Mounting

Compatible Post:

M4 x0.7

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Contains SVHC\(s\)](#)

Product Details

[Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

- FC Fiber Connection
- Two Axis Linear Movement for Precise Fiber Alignment
- Optional Kinematic Tilt Version
- [Posts](#) and [Post Holders](#) Required for Mounting

Fiber Optic Alignment Mounts can translate optical fibers terminating in an FC connection. Useful for telecom positioning and for aligning FC Fiber Optic Patchcords, they feature $\pm 1.5\text{mm}$ travel in both the X and Y-axis. The Differential Micrometer models feature 2.5 micron resolution while the kinematic version ([#55-478](#)) provides an additional $\pm 2^\circ$ tilt adjustment on each axis.

Note: [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

Technical Information

