

[See all 6 Products in Family](#)

200 x 260mm Sheet of Fractal Black Foil, Low Outgassing Adhesive

See More by [Acktar](#)



Stock #75-436 NEW **2 In Stock**

⊖ 1 ⊕ C\$477⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$477.40 each
Need More?	Request Quote

Product Downloads

General

FBC-20X26-2 **Model Number:**

Low Outgassing Adhesive **Type:**

Note:
Typical Adhesive Outgassing Performance: 0.85%
TML, 0% VCM per ASTM E595-77/84/90

Physical & Mechanical Properties

200 x 260 **Dimensions (mm):**

100	Foil Thickness (µm):
60	Adhesive Thickness (µm):
4.00	Thickness (mm):

Optical Properties

Fractal Black™	Coating:
Copper	Substrate: □
<5	Coating Thickness (µm):
VIS - FIR	Wavelength Range (µm):

Environmental & Durability Factors

-50 to +150	Operating Temperature (°C):
Moderate	Abrasion Resistance:
ML-C-48497A	Humidity Resistance:

Regulatory Compliance

View	Certificate of Conformance:
----------------------	------------------------------------

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Copper Foil Increases Thermal and Electrical Conductivity
- Consistent Performance in High Temperature Environments
- Standard, Low Outgassing, and No Adhesive Options Available

Acktar Fractal Black on Copper Foils provide thermal management and light absorption for applications where direct coating is not feasible. The addition of copper foil enhances the thermal and electrical conductivity of Fractal Black, making it ideal for applications in laser devices and platforms, passive and thermal control, IR systems, space, and vacuum. The foil is designed to be flexible, lightweight, and easily cut to size for simple application and installation on a variety of surfaces. Acktar Fractal Black on Copper Foils is available in standard, low outgassing, and no adhesive options.