

## 20.0mm Beam Steering Assembly



#67-363

Stock **#67-363** **3 In Stock**

⊖ 1 ⊕ C\$652<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-10	C\$652.40 each
Qty 11+	C\$607.74 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Adjustable - Beam Steering **Type:**

Circular **Type of Optics:**

360° Horizontal, 6° Tilt **Range:**

#### Physical & Mechanical Properties

**Construction:**

Post Diameter (mm):

20.0

## Threading & Mounting

Size of Compatible Optics (mm):

25.0 - 25.4

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Ready to Use Beam Steering Assembly
- High Resolution 100 TPI Kinematic Mounts
- Available with 20mm Post for Higher Stability

Beam Steering Assemblies are specifically suited for numerous applications in laser holography, interferometry and other exacting set-ups and systems requiring precise redirection of an optical beam. The 12.7mm Beam Steering Assembly comprises a slotted base, suitable for attachment to metric and imperial bench plates, a main 300mm post and two 100 TPI kinematic mounts with 6° tilt range, suitable for 1" or 25mm diameter optics. The kinematic mounts can be moved vertically and can also be rotated 360° around the main post. The 20mm Beam Steering Assembly is designed for applications that require a higher level of stability and feature a larger slotted base than its 12.7mm counterpart; it includes a 20mm main post and heavy duty cross clamps. Mirrors are held in place with an #8 set screw.

## Technical Information

